HORIBA



HORIBASTEO

Digital Mass Flow Controller

SEC-N100 series





EtherCAT® model EtherCAT®

SEC-N107 Fitting to fitting 124mm-



PROFIBUS™ model 24 V DC, 4 - 20 mA SEC-N106 Fitting to fitting 124mm-



CC-Link™ model CC-Link SEC-N105 Fitting to fitting 124mm-





DeviceNet™ model



SEC-N104 Fitting to fitting 124mm- SEC-N104W Fitting to fitting 106mm-



Digital/Analog model SEC-N102 Fitting to fitting 124mm SEC-N102W Fitting to fitting 106mm



A variety of communication, fitting-to-fitting dimensions and flow control ranges to suit customer needs.

HORIBA STEC has built an enviable reputation in markets throughout the world by delivering products with superior performance specifications and excellent reliability.

The SEC-N100 Series of mass flow controllers from HORIBA STEC is designed for use in a wide range of applications ranging from the controlled delivery of process gases for solar cell manufacturing to high accuracy bench-top gas blending. Our considerable experience and expertise in the measurement and control of gases for all applications is reflected in the development of our industry-leading-edge SEC-N100 Series which is available in with digital/analog, DeviceNetTM, CC-LinkTM, PROFIBUSTM, and EtherCAT® communication as well as a variety of fittings, sizes and flow rate control ranges.

Multiple Configulation Options

Communication options include digital/analog, DeviceNet™, CC-Link™, and PROFIBUS™. A choice of two fitting-to-fitting dimensions is provided: 124 mm - and 106 mm - (W Type)*. The flow rate control range extends from 10 SCCM to 1000 SLM, SEC-N100 Series is suitable for a wide variety of applications where gas control is required.

*W Type are appl icable SEC-N102 (Digital/Analog communication model) and SEC-N104 (DeviceNet™ communication model).

*Fittings is 1/4" VCR equivalent.

		Flow rate control range (Full-scale flow rate)				
		10 sccм 10 slм	50 slm	100 slm	200 slm	1000 slm
Digital communication ▶RS485 F-Net Protocol Analog communication ▶0 - 5 V DC	SEC-N102 (Fitting to fitting) 124mm—	SEC-N112	SEC-N122	SEC-N132 Fitting to fitting: 132 mm—	SEC-N142 Fitting to fitting: 132 mm—	SEC-N172
 Power supply ±15 V DC (±5%) Dedicated power supply PE Series are aveirable. 	SEC-N102W (Fitting to fitting) 106mm—	SEC-N112W	SEC-N122W	_		
DeviceNet TM communication	SEC-N104 (Fitting to fitting) 124mm—	SEC-N114	SEC-N124	SEC-N134 Fitting to fitting: 132 mm—	SEC-N144 Fitting to fitting: 132 mm —	SEC-N174
► Conforming to ODVA standard	SEC-N104W (Fitting to fitting) 106mm—	SEC-N114W	SEC-N124W	_		
CC-Link [™] communication CC-Link Analog communication ▶0-5 V DC, 0-10 V DC, 4-20 mA Power supply 24 V DC (13-32 V DC)	SEC-N105 (Fitting to fitting) 124mm-	SEC-N115	SEC-N125	SEC-N135 Fitting to fitting: 132 mm—	SEC-N145 Fitting to fitting: 132 mm —	SEC-N175
PROFIBUSTM communication PROFID Analog communication 0-5 V DC, 0-10 V DC, 4-20 mA Power supply 24 V DC (13-32 V DC)	SEC-N106 (Fitting to fitting) 124mm-	SEC-N116	SEC-N126	SEC-N136 Fitting to fitting: 132 mm—	SEC-N146 Fitting to fitting: 132 mm —	SEC-N176
EtherCAT® communication EtherCAT®	SEC-N107 (etting to fitting) 124mm-	SEC-N117	SEC-N127	_	_	SEC-N177

- Standard fitting of SEC-N11x(R) and SEC-N12x(R) is 1/4" VCR equivalent. Standard fitting of SEC-N13x and SEC-N14x is 1/2" VCR equivalent.
- Flow rate control: available from 2% of full scale flow rate. (SEC-N17x: from 5%)



[High accuracy]

High S.P. accuracy


MFC's linearity is compensated using a polynomial approximated curve. This achieves high accuracy for all flow control ranges. Each process gas is individually characterized in the HORIBA STEC standard gas measurement system using the actual gas - not a reference or surrogate gas. : 30-100% F.S.

Accuracy

±1.0% S.P.

±0.3% F.S. : ≤30% F.S.

(SEC-N11X(W)/N12X(W))




 $y=ax^5+bx^4+cx^3+dx^2+ex+f$



[High-speed response throughout the flow rate range]

New variable PID algorithm: 1 second high-speed response

SEC-N100 Series uses the latest "Variable PID system", which enables 1 second response to all set-points. This system changes the PID continuously for optimum response to flow setting changes, ensuring fast response even when the full scale range or specified gas is changed using the SEC-Z500X Software.




Response speed



[Multi-range, multi-gas solution]

Exclusive software allows users to easily alter MFC configuration

Users can modify the full-scale range or gas type using a simple PC connection.



Suitable for multiple type of gas

Easily change a type of gas

Example: SEC-N100 MR·MG-02

Suitable of multiple ranges


Easily change a full-scale flow rate control range.

Example: SEC-N100 MR·MG-04



Exclusive software: Configuration Software

This software makes it possible to select MR & MG numbers simply by entering the type of gas being used and the flow rate range, and also features a handy N_o gas conversion feature for flow rate measurements using N₂ gas during receipt inspections.



*Use a dedicated cable with the CC-Link™ communication model. (Optional)

To ensure that the software is used without error, HORIBA STEC offers software operation seminars, please contact your HORIBA STEC representative.

▶ Common specifications

	SEC-N112MGM	SEC-N112MGR(W)	SEC-N122MGM	SEC-N122MGR(W)				
	SEC-N114MGM	SEC-N114MGR(W)	SEC-N124MGM	SEC-N124MGR(W)				
Mass Flow controller model	SEC-N115MGM	SEC-N115MGR	SEC-N125MGM	SEC-N125MGR				
	SEC-N116MGM	SEC-N116MGR	SEC-N126MGM	SEC-N126MGR				
	SEC-N117MGM	SEC-N117MGR	SEC-N127MGM	SEC-N127MGR				
	SEF-N112MGM	SEF-N112MGR(W)	SEF-N122MGM	SEF-N122MGR(W)				
	SEF-N114MGM	SEF-N114MGR(W)	SEF-N124MGM	SEF-N124MGR(W)				
Mass Flow meter mode								
Wass Flow Meter Mode	SEF-N115MGM	SEF-N115MGR	SEF-N125MGM	SEF-N125MGR				
	SEF-N116MGM	SEF-N116MGR	SEF-N126MGM	SEF-N126MGR				
	SEF-N117MGM	SEF-N117MGR	SEF-N127MGM	SEF-N127MGR				
Full-scale flow rate (N₂ conversion flow rate) Full scale flow ranges are distinguished by BIN number except SEC(F)-N17xR Full scale flow ranges are distinguished by BIN number except SEC(F)-N17xR R01: 10SCCM R1.5: 17.5SCCM 01: 30SCCM 04: 1SLM 05: 3SLM 02: 100SCCM 05: 3SLM 05: 5.5SCLM		4.5 : 1.75SLM 05 : 3SLM	6.5: 2: 07 : 3: 08 : 5:	0 SLM				
Valve type		C: Norma	ally close					
Flow rate at fully closed control valve		≤2%	F.S.					
Flow rate control range		2-100%	of F.S.					
Flow rate measuring range (SEF)		0-100%						
Accuracy *1		±1.0% S.P. (Flow ±0.3% F.S. (Flow	·					
Operating temperature		5 to 50°C (recommended ten	nperature range: 15 to 45°C)					
Response		≤1 second: over f	ull flow rate range					
Linearity		≤±0.5						
Repeatability		≤±0.2	% F.S.					
Operating differential pressure	50 to 300 MR.MG-5.5, 06: 1	(/	200 to 30	00 kPa (d)				
Operating differential pressure (SEF)		≤300 k	«Pa (d)					
MAX. Operating pressure		450 k						
Pressure resistance		1000 k						
Leak integrity	≤5x10 ⁻¹² Pa•m³/s (He)	≤1x10 ⁻¹⁰ Pa•m³/s (He)	≤5x10 ⁻¹² Pa∙m³/s (He)	≤1x10 ⁻¹⁰ Pa•m³/s (He)				
Wetted materials	SUS316L PTFE magnetic stainless *2	SUS316L PTFE magnetic stainless *2 Elastomer	SUS316L PTFE magnetic stainless *2	SUS316L PTFE magnetic stainless *2 Elastomer				
		Elasioniei	1/4 inch VCR equivalent, 1/4 inch Swagelok equivalent *3					
Standard fitting			inch Swagelok equivalent *3	LIGOTOTTO				

¹ The precision is that associated with the full-scale MR and MG number values. The flow rate precision guaranteed temperatures conform to SEMI standards. For details, please contact HORIBA STEC.

7.0 VA

► Communication/power supply


Digital/Analog communication model

SEC-N102(W)

Mass Flow controller model	SEC-N112MGM	SEC-N112MGR(W)	SEC-N122MGM	SEC-N122MGR(W)	SEC-N132MGM	SEC-N132MGR	SEC-N142MGM	SEC-N142MGR	SEC-N172R
Mass Flow meter model	SEF-N112MGM	SEF-N112MGR(W)	SEF-N122MGM	SEF-N122MGR(W)	SEF-N132MGM	SEF-N132MGR	SEF-N142MGM	SEF-N142MGR	SEF-N172R
Flow rate setting signal		0.1 to 5 V DC (2% to F.S.); input impedance $1M\Omega$ or higher					•		
Flow rate output signal		0 to 5 V DC (0% to F.S.); minimum load resistance $2k\Omega$							
Digital interface		With address function: RS-485 (transmission speed 38400bps) F-NET Protocol							
Power supply		% 150 mA % 200 mA		% 150 mA % 250 mA		+15 V ±59 -15 V ±59			+15 V ±5% 150 mA -15 V ±5% 200 mA

DeviceNet™ communication model

SEC-N104(W)



CC-Link™ communication/Analog communication SEC-N105



7.0 VA

4.0 VA

CODYA

OLO IIIIO									
Mass Flow controller model	SEC-N115MGM	SEC-N115MGR	SEC-N125MGM	SEC-N125MGR	SEC-N135MGM	SEC-N135MGR	SEC-N145MGM	SEC-N145MGR	SEC-N175R
Mass Flow meter model	SEF-N115MGM	SEF-N115MGR	SEF-N125MGM	SEF-N125MGR	SEF-N135MGM	SEF-N135MGR	SEF-N145MGM	SEF-N145MGR	SEF-N175R
Flow rate setting signal			0.1	to 5 V DC/0.2 to	10 V DC/4.32 to	20 mA (2% to F	S.)		_
Flow rate output signal		0 to 5 V DC/0 to 10 V DC/4 to 20 mA (0% to F.S.)							
Digital interface	By CC-Link™ Protocol station type: Remote device station; Occupied station: 1 occupied station; CC-Link™ version: Ver. 1.10				1.10				
Power supply				24 \	/ DC (13 to 32 V	DC)			
		7.5 VA 4.5 VA 4.5 VA 7.5 VA						7.5 VA	

^{*2} Neither PTFE nor magnestic stainless steel are used for mass flow mater.

*4 3/8" Swagelok equivalent is applicable with SEC-N13×R, SEC-N14×R.

*5 Outlet pressure is required 0 kPa (g) or higher.

SEC-N132MGM	SEC-N132MGR	SEC-N142MGM	SEC-N142MGR	SEC-N172R			
SEC-N134MGM	SEC-N134MGR	SEC-N144MGM	SEC-N144MGR	SEC-N174R			
SEC-N135MGM	SEC-N135MGR	SEC-N145MGM	SEC-N145MGR	SEC-N175R	Mass Flow controller model		
SEC-N136MGM	SEC-N136MGR	SEC-N146MGM	SEC-N146MGR	SEC-N176R			
		<u>_</u>		SEC-N177R			
SEF-N132MGM	SEF-N132MGR	SEF-N142MGM	SEF-N142MGR	SEF-N172R			
SEF-N134MGM	SEF-N134MGR	SEF-N144MGM	SEF-N144MGR	SEF-N174R			
SEF-N135MGM	SEF-N135MGR	SEF-N145MGM	SEF-N145MGR	SEF-N174R SEF-N175R	Mana Flancosatan ana dal		
					Mass Flow meter model		
SEF-N136MGM	SEF-N136MGR	SEF-N146MGM	SEF-N146MGR	SEF-N176R			
-	-	-	-	SEF-N177R			
09: 10	00 SLM	10 : 20	DO SLM	300/500/1000SLM	Full-scale flow rate $(N_2$ conversion flow rate) Full scale flow ranges are distinguished by BIN number except SEC(F)-N17xR		
	C: Norma ll y close	O: Normally open		Normally close	Valve type		
		F.S.		≤5% F.S.	Flow rate at fully closed control valve		
	2-100%			5-100% of F.S.	Flow rate control range		
		0-100% of F.S.			Flow rate measuring range (SEF)		
	±1.0% S.P. (Flow ±0.35% F.S. (Flov	v rate ≤ 35% F.S.)		±2.0% F.S.	Accuracy *1		
		mmended temperature rang	ge: 15 to 45°C)	Operating temperature			
		ull flow rate range		≤2 second (T98)Typical	Response		
		% F.S.		≤1.0% F.S.	Linearity		
100 to 3	≤±0.2 00 kPa (d)		≤1.0% F.S. 150 to 300 kPa (d) 200 to 300 kPa (d) 250 to 350 kPa (d) (1000 SI		Repeatability Operating differential pressure		
	≤300	kPa (d)		≤350 kPa (d)	Operating differential pressure (SEF)		
		Pa (g)		350 kPa (g)	MAX. Operating pressure		
		1000 kPa (g)			Pressure resistance		
≤5x10 ⁻¹² Pa•m³/s (He)	≤1x10 ⁻¹⁰ Pa•m³/s (He)	≤5x10 ⁻¹² Pa•m³/s (He)	≤1x10 ⁻¹⁰ Pa•m³/s (He)	≤1x10 ⁻⁷ Pa•m³/s (He)	Leak integrity		
SUS316L	SUS316L Elastomer	SUS316L	SUS316L Elastomer	SUS316/SUS304 PTFE magnetic stainless *2 Elastomer	Wetted materials		
	1/2 inch VCR equivalent, 3/8 inch Swagelok equivalent *4 1/2 inch Swagelok equivalent, 1/2 inch Swagelok equivalent						
	Free						
	-						

- SCCM, SLM are numbers that represents flow rate (mL/min, L/min, at 0°C101.3 kPa).

 Note that components or production methods may be modified for productivity reasons at any time without notice provided that such modification does not alter the product specifications.

PROFIBUS™ communication/Analog communication SEC-N106



Mass Flow controller model	SEC-N116MGM	SEC-N116MGR	SEC-N126MGM	SEC-N126MGR	SEC-N136MGM	SEC-N136MGR	SEC-N146MGM	SEC-N146MGR	SEC-N176R
Mass Flow meter model	SEF-N116MGM	SEF-N116MGR	SEF-N126MGM	SEF-N126MGR	SEF-N136MGM	SEF-N136MGR	SEF-N146MGM	SEF-N146MGR	SEF-N176R
Flow rate setting signal		0.1 to 5 V DC/0.2 to 10 V DC/4.32 to 20 mA (2% to F.S.)							
Flow rate output signal		0 to 5 V DC/0 to 10 V DC/4 to 20 mA (0% to F.S.)							
Digital interface		PROFIBUS™-DP Protocol							
D				24 \	/ DC (13 to 32 V	DC)			
Power supply		7.5	- VA			4.5	VA		7.5 VA


EtherCAT® communication mode **SEC-N107**



OLO NIO/						
Mass Flow controller model	SEC-N117MGM	SEC-N117MGR	SEC-N127MGM	SEC-N127MGR	SEC-N177R	
Mass Flow meter model	SEF-N117MGM	SEF-N117MGR	SEF-N127MGM	SEF-N127MGR	SEF-N177R	
Digital interface			EtherCAT® Protocol			
Device comple	24VDC±4V					
Power supply		7.2VA				

▶ Selecting a model

SEC-N100




► Gas and full-scale flow rate table (e.g.)

(applicable with SEC-N100R)
8IS: 1/2" Swagelok male type fitting (applicable with SEC-N17×)

type of gas	N_2	Ar	$H_{\!\scriptscriptstyle 2}$	He	CO ₂	CH₄
	ı N114(W), SEC-N115, SEC-N	□ N116, SEC-N117				
R01	3-10	4-11	3-10	4-12	3-8	2-7
R1.5						
01	8-30	11-35	8-30	10-38	7-25	6-22
1.5						
02	25-100	35-110	25-100	33-120	21-83	19-75
2.5						
03	75-300	110-350	75 - 300	99-380	64-250	57-220
3.5						
04	250-1000	350-1100	250-1000	330-1300	210-830	190-750
4.5						
05	750-3000	1100-3500	750-3000	1100-4100	610-2400	590-2300
5.5						
06	2500-10000	3500-11000	2500-10000	3900-13000	2000-8000	2000-7800

Gases shown above are for reference only. Software includes data for gases/mixtures other than those listed above.

SEC-N100W



type of gas	N ₂	Ar	H ₂	He	CO ₂	CH₄
SEC-N122(W), SEC-	N124(W), SEC-N125, SEC-N	V126, SEC-N127				
6.5						
07	10000-30000	10000-30000	10000-30000	12000-30000	7300-21000	5800-22000
08	30000-50000	30000-50000	30000-50000	30000-50000	21000-35000	22000-38000
SEC-N132, SEC-N13	34, SEC-N135, SEC-N136					
09	50000-100000	50000-95000	50000-100000	50000-108000	35000-75000	38000-76000
SEC-N142, SEC-N14	44, SEC-N145, SEC-N146					
10	100000-200000	95000-176000	100000-200000	108000-200000	75000-158000	76000-152000

• Gases shown above are for reference only. Software includes data for gases/mixtures other than those listed above.

Unit:SCCM

▶ Analog communication

Using an external power source and control signal



Signal cable SC-EAH Series is applicable with SEC-N102(W)

SEC-N102(W) Analog connector


Pin No.	name of signnal
1	Compulsory valve open/close signal *1
2	Flow rate output signal 0 to 5 V DC (minimum load resistance 2kΩ)
3	Power supply: +15 V DC
4	Power supply : common *2
5	Power supply : -15 V DC
6	Flow rate setting signal : 0 to 5 V DC (input impedance 1MΩ or higher) *1
7	Signal: common *2
8	Signal: common *2
9	Valve position monitoring *1

Connector used: D-subminiature 9-contact-pin (with M3 fastening screws)

- *1 Mass Flow meter is N.C.
- *2 The pin No.4 common power source and pin No.7 common signal should be connected at the GND side of power supply for preventing change of common voltage by valve power supply.

No.7 and No.8 common signal are connected inside.

Using various functional power control unit, PE-S7



Signal cable SC-EDH Series is applicable with SEC-N102(W)

SEC-N105, SEC-N106 Analog connector

Pin No.	name of signnal	
1	Compulsory valve open/close signal	*1
2	Flow rate output signal	
3	Power supply (13 to 32 V DC)	*2
4	Signal : common	
5	Power supply : common (0 V DC)	*2
6	Flow rate setting signal	*1
7	Flow rate output signal :common	
8	Flow rate setting signal :common	
9	Valve position monitoring	*1

Connector used: D-subminiature 9-contact-pin (with #4-40 UNC inch screws)

- *1 Mass Flow meter is N.C.
- *2 Power circuit and input-output adapter are isolated.
- * Impedance of flow rate setting signal input


0 to 5 V DC, 0 to10 V DC: 1M Ω , 4 to 20 mA: 250 Ω

Load resistance of flow rate output signal

0 to 5 V DC : Minimum load resistance 2k Ω , 0 to10 V DC: minimum load resistance: 5k Ω

4 to 20 mA : Maximum load resistance 250 Ω

▶ Digital communication




RS485 digital communication

•	
Pin No.	name of signnal
1	Digital signal : common
2	Digital signal : common
3	N.C.
4	Serial output (-)
5	Serial output (+)
6	N.C.
7	N.C.
8	N.C.

Connector used: RJ45 connector


▶ DeviceNet[™] communication




DeviceNet™ communication

DeviceNet™ is an open and global field network that was developed by the ODVA (Open DeviceNet™ Vendors Association, Inc.) as a unique means for supporting standardization worldwide. The ODVA offers EDS (Electronic Data Sheet) specifications, which are designed to allow shared operability and programming on a multi-vendor environment. The ODVA also carries out conformance testing. Device that have passed the ODVA's conformance testing can display the **DODYA** logo.

▶ CC-Link[™] communication



CC-Link™ communication



MFC main unit connector: DMC, 5/5-G1F3, 5-LR P20THR 5 stations* two stage type

Electrical supply connector


Pin No.	name of signal
1	N.C.
2	N.C.
3	Power supply +24V DC (13-32V DC)
4	N.C.
5	Power supply return 0 V DC
6	N.C.
7	N.C.
8	N.C.
9	N.C.

Connector used:
D-subminiature 9 pin Male type
(#4-40 LINC inch screws)

CC-LinkTM communication is an or

CC-Link™ communication is an open high-speed field network that processes both control and information at the same time. As responsiveness at high speeds of up to 10 Mbps has been achieved, CC-Link™ ensures communication reliability. Because the link scan time obtained in an actual CC-Link™ system is almost equal to the calculated value, communication with sensor inputs that require high-speed response or intelligent devices that require high-bandwidth data communications can be flexibly supported. Based in Japan, the CC-Link™ Partner Association has operational sites in six world regions, including Asia, and is a global leader in promoting CC-Link™, an open-architecture industrial network.

▶ PROFIBUS™ communication



PROFIBUS™ communication connector

Pin No.	name of signal
1	N.C.
2	N.C.
3	RXD/TXD-P
4	CNTR-P
5	Digital ground
6	V.P.
7	N.C.
8	RXD/TXD-N
9	N.C.

Connector used:
D-subminiature 9-contact-socket connector (with #4-40 UNC inch screws)

Electrical supply connector


name of signal
N.C.
N.C.
Power supply +24V DC (13-32V DC)
N.C.
Power supply return 0 V DC
N.C.
N.C.
N.C.
N.C.

Connector used: D-subminiature 9 pin Male type (#4-40 UNC inch screws)

PROFIBUS™ communication

PROFIBUS™ is an open field bus that is certified IEC61158. It is composed of PROFIBUS™-DP for factory automation and PROFIBUS™ PA for process automation. PROFIBUS™ Organization supports standardization worldwide.

▶ EtherCAT® communication



What is EtherCAT® communication?

Open field bus system based on Ethernet. ETG (EtherCAT® Technology Group) has been established as an international forum to promote support and diffusion of EtherCAT®, and maintain mutual compatibility. ETG specifies functional requirements, conformance tests and its certification procedure, and permits only devices which satisfy conditions specified by ETG to use the EtherCAT logo.

Power connector



Pin No.	Signal name
1	V+
2	N.C.
3	Power Common
4	N.C.
5	N.C.


Connector used: M8 5pin male connector

* Use connectors that conform to the EtherCAT® Technology Group standard: ETG5003.2020.

Features

- · High bus efficiency and high-speed data scan is realized by simultaneously communicating with many devices.
- · The master can use the standard Ethernet interface when connecting to devices, and does not require expensive dedicated hardware.


▶ Digital/Analog model



Code	Name	Account					
Α	Digital transmission connector RS-485 communication. Daisy chain connection is a						
В	Analog connector Provision of power supply. For analog transmission						
С	ZERO adjust switch Switch for correcting ZERO-point						
D	Address setting switch It is possible to set in the range of 0x01 to 0x99						
Е	Indicator LED	While analog communication, green lights turns on.					
		(When alarm and incorrect ZERO-point, red lights turn on)					

▶ DeviceNet™ model


SEC-N104(W)



Code	Name	Account				
F	DeviceNet™connector	For DeviceNet™ communication. Shield Micro-connector				
G	Transmission setting switch	Transmission speed setting				
Н	ZERO adjust switch Switch for correcting ZERO-point					
1	Address setting switch It is possible to set in the range of 00 to 63					
J	Indicator LED	NET: it represents condition of network.				
		MOD: it represents conditon of node.				


▶ CC-Link™ model

SEC-N105




Code	Name	Account				
K	CC-Link™ connector	For CC-Link™ communication				
L	ZERO adjust switch	Switch for correcting zero-point				
М	Rotary switch for setting station number	It is possible to set in the range of 1 to 64				
N	LED for communication status	Indicates CC-Link™ communication status				
0	Rotary switch for setting communication speed	It is possible to set in the range of 0 to 4				
Р	Connector for power supply/ analog communication	Provision of power supply for analog communication.				

▶ PROFIBUS™/Analog model




Code	Name	Account				
Q	PROFIBUS™ Connector	For PROFIBUS™ communication				
R	ZERO adjust switch	Switch for correcting ZERO-point				
s	Address setting switch	It is possible to set in the range of 0×01 to 0×7D				
Т	Indicator LED	NET: it represents condition of network.				
		MOD: it represents conditon of node.				
U	Analog connector	Provision of power supply.				
		For analog communication				


► EtherCAT® communication model



Symbol	Name	Explanation				
а	Power connector	Drive power supply connector				
b	DIAG communication port	Service communication port				
С	EtherCAT® ID selector	Settable in a range from 0x0000 to 0x0FFF				
		 If this ID is used for EtherCAT® communication, it is required to perform a predetermined initial setting. If you have any question about how to set up, please contact us. 				
d	ZERO adjust switch	Zero adjust switch				
е	EtherCAT® IN port	For EtherCAT® communication. Connection on IN side				
f	EtherCAT® OUT port	For EtherCAT® communication. Connection on OUT side				
g	MFC indicator LED	Indicates MFC state.				
		Normal: Turns on in green				
		Abnormal: Turns on in red or flashes in red/green depending on abnormal cause.				
h	EtherCAT® indicator LED	ECAT ERR: Indicates error state of EtherCAT® communication.				
		POWER: Turns on in green when power is supplied.				
		LA: Indicates link/active state of each port.				
		RUN: Indicates state of EtherCAT® state machine.				

External dimensions





and all	н	т	w	I				D	position of fastened	
model	"		, vv	1/4" VCR type	1/4" SWL type	1/2" VCR type	3/8" SWL type	1/2"SWL type	<u> </u>	screws
SEC(F)-N112	126±1	30.5±0.5	81.8	124±1(4CRL)	132	_	_	_	12.7	See above diagram (A)
SEC(F)-N122	12021	00.020.0	01.0	1241 (4011)					12.7	occ above diagram &
SEC(F)-N112W	126±1	38±0.5	63.8	106±1	127	_	_	_	12.7	See above diagram ®
SEC(F)-N122W	12021	00=0.0	00.0	10021					16.1	See above diagram ©
SEC(F)-N132	139±1	38.3±0.5	70.4(1/2" VCR type)	_	_	132(8CRS) 150.4(8CRJ)	150.4(6ISJ)	_	18.5(1/2" VCR type)	See above diagram
SEC(F)-N142	100=1	0010-010	94.4(3/8" SWL type)			177(8CRG)	179(6ISH)		22(3/8" SWL type)	See above diagram ®
SEC(F)-N114	126±1	30.5±0.5	81.8	124±1(4CRL)	132	_	_	_	12.7	See above diagram (A)
SEC(F)-N124	12021	00.020.0	01.0	12121(10112)					16.1	Occ above diagram
SEC(F)-N114W	126±1	38±0.5	63.8	106±1	127	_	_	_	12.7	See above diagram ®
SEC(F)-N124W		00-0,0		100-1						See above diagram ©
SEC(F)-N134	150±1	38.3±0.5	70.4(1/2" VCR type)	_	_	132(8CRS) 150.4(8CRJ)	150.4(6ISJ)	_	18.5(1/2" VCR type) 22(3/8" SWL type)	See above diagram
SEC(F)-N144	100-1	00.0-0.0	94.4(3/8" SWL type)			177(8CRG)	179(6ISH)	_		See above diagram ®
SEC(F)-N115	132±1	30.5±0.5	81.8	124±1(4CRL)	132	_	_	_	12.7	See above diagram @
SEC(F)-N125		00.0-0.0	07.10	121-1(10112)						See above diagram ©
SEC(F)-N135	139±1	38.3±0.5	70.4(1/2" VCR type)	_	_	132(8CRS) 150.4(8CRJ)	150.4(6ISJ)	_	18.5(1/2" VCR type)	See above diagram
SEC(F)-N145			94.4(3/8" SWL type)			177(8CRG)	179(6ISH)		22(3/8" SWL type)	See above diagram ®
SEC(F)-N116	132±1	30,5±0,5	30.5±0.5 81.8	124±1(4CRL)	132	_	_	_	12.7	See above diagram @
SEC(F)-N126										
SEC(F)-N136	139±1	38,3±0,5	38.3±0.5 70.4(1/2" VCR type)	_	_	132(8CRS) 150.4(8CRJ)	150.4(6ISJ)	_	18.5(1/2" VCR type)	See above diagram
SEC(F)-N146			94.4(3/8" SWL type)			177(8CRG)	179(6ISH)		22(3/8" SWL type)	See above diagram ©
SEC(F)-N117	132±1	30,5±0,5	81.8	124±1 (4CRL)	_	_	_	_	12.7	See above diagram (A)
SEC(F)-N127										_
SEC-N172R	171±1									
SEC-N174R		75	128±2	-	_	203±2(8CRI)	_	209.4(8ISR)	37.5	See above diagram ©
SEC-N175R	177±1	7±1								
SEC-N176R										
SEC-N177R	180±1	75	128±2	_		203±2(8CRI)	_	209.4(8ISR)	37.5	See above diagram ©
SEF-N172R	75 177±1									
SEF-N174R			-	-	159±2(8CRP)	_	165.6(8ISC)	37.5	See above diagram ⊕	
SEF-N175R										
SEF-N176R										
SEF-N177R	180±1	75	84±2	_	_	159±2(8CRP)	_	165.6(8ISC)	37.5	See above diagram ⊕ (Unit:mm)

Multifunctional controller

PE-S7

The PE-S7, which comes with a program setting function, a preset function, and an integration function, is a RoHS-compliant multifunctional controller. Its front control panel offers improved ease of use.

■Specifications

• Multi-range solution ● flow rate setting function/6 presets ● program control function ● flow rate display ● integration flow rate alarm function, external output: open connector ● soft-start function, soft-start: ≤60 second, slow-start: ≤1200 second ● flow rate output signal: 0 to 5 V DC external control function, flow rate setting signal input, flow rate control valve signal input: fully open/fully closed ● power supply input: 100 V AC to 240 V, 50/60Hz 30 VA MAX ● dimensions: 48(W)x192(H)x190(D) mm (except projection portion) ● conforming to CE marking, EMC, FCC, and PSE. RoHS compliant ● conforming to digital/analog transmission model



Dedicated power supply

PE Series

The PE series provides a power supply to drive mass flow controllers/meters and auto pressure regulator with a reference voltage of 5 V DC for analog control. A model supporting current control (4–20 mA), a model with a flow rate alarm output, and a model that can drive more than one unit (4 or 6 units) are also available. All the models comply with the CE marking safety standard, the EMC Directive, the FCC, the Electrical Appliance and Material Safety Act, and the RoHS Directive so as to protect the environment.



▶ Standard model PE-20 Series

Conforming to digital/analog transmission

Power supply input:100-240 V AC 50/60Hz 1 unit drive PE-21 (30 VA MAX) 4 units drive PE-24 (90 VA MAX) 9 units drive PE-26 (140 VA MAX)

▶ Alarm model PE-30A Series

- High/low flow rate alarms
- Digital/analog solution.

▶ Current control model PE-30S Series

- Current control: 4 to 20 mA. Analog signal enable to long-distance control.
- High/low flow rate alarms
- Digital/analog solution.


Power source: 100-240 V AC 50/60Hz
1 unit driving PE-31S (30 VA MAX)
4 units driving PE-34S (90 VA MAX)

▶ Structure and operating principles of digital mass flow controller

The general structure of the SEC-N100 Series of mass flow controller is shown in the diagram to the right. These mass flow controllers have flow rate measurement section that includes a sensor, bypass, flow rate control valve, and special circuitry. A CPU is part of the circuitry, which makes it both multi-functional and highly efficient.

The gas is input from an inlet joint, and is divided so that it flows over both the flow rate sensor and a bypass. The sensor measures the mass flow rate of the gas, and the flow rate control valve modifies the flow rate so that the difference between the measured flow rate and the flow rate received from the external flow rate setting signal is 0 (zero).

The units feature a loop circuit, so even if there is a secondary pressure change or ambient temperature change that could affect the supply pressure of the introduced gas, the flow rate is instantaneously corrected, which ensures stable flow rate control.





The HORIBA Group adopts IMS (Integrated Management System) which integrates Quality Management System ISO9001, Environmental Management System ISO14001, and Occupational Health and Safety Management System OHSAS18001. We have now integrated Business Continuity Management System ISO22301 in order to provide our products and services in a stable manner, even in emergencies.



Applying to the EU RoHS Directive: This products is compliant with the restriction of the designated 6 hazardous substances(*). (*) lead, cadmium, mercury, hexavalent chromium, polybrominated biphenyls (PBB) and polybrominated diphenyl ethers (PBDE)

Using lead-free soldering: Lead-free soldering is used for mounting components of printed circuit boards.

- Many countries consider the reinforcement of regulations concerning the risk caused by lead to human body and the environment
- The contents of this catalog are subject to change without prior notice, and without any subsequent liability to this company.
- It is strictly forbidden to copy the content of this catalog in part or in full.
- All brand names, product names and service names in this catalog are trademarks or registered trademarks of their respective companies.

HORIBASTEO HORIBA STEC, Co., Ltd.

http://www.horiba.com/horiba-stec/



Please read the operation manual before using this product to ensure safe and proper handling of the product.

HEAD OFFICE

11-5, Hokodate-cho, Kamitoba, Minami-ku, Kyoto, 601-8116 Japan PHONE: (81)75-693-2312 FAX: (81)75-693-2331

U.S.A. HORIBA Instruments Incorporated

Sunnyvale Head Office (Technology Center)
PHONE: (1)408-730-4772 FAX: (1)408-730-8975 Austin Office

PHONE: (1)512-836-9560 FAX: (1)512-836-8054

Portland Office PHONE: (1)503-624-9767 FAX: (1)503-968-3236

Reno Office (R&D Center) PHONE: (1)775-358-2332 FAX: (1)775-358-0434

Albany Office PHONE: (1)518-331-1371

SINGAPORE

HORIBA Instruments (Singapore) Pte Ltd.
PHONE: (65)6-745-8300 FAX: (65)6-745-8155

KOREA HORIBA STEC KOREA, Ltd. PHONE:(82)31-8025-6500 FAX: (82)31-8025-6599

TAIWAN HORIBA Taiwan, Inc.PHONE: (886)3-560-0606 FAX: (886)3-560-0550

Tainan OfficePHONE: (886)6-583-4592 FAX: (886)6-583-2409

CHINA HORIBA (China) Trading Co., Ltd.

Beijing office PHONE: (86)10 85679966 FAX: (86)10 85679066 **Shanghai office**PHONE: (86)21 62896060 FAX: (86)21 62895553

Shanghai service center PHONE: (86)21 51317150 FAX: (86)21 51317660

Chengdu office PHONE: (86)18583234999

Xi'an office PHONE: (86)029 88868480 FAX: (86)029 88868481 Shenzhen office PHONE: (86)13602530661

HORIBA UK Ltd. Northampton office PHONE: (44)1604 542600 FAX: (44)1604 542696

FRANCE HORIBA UK Ltd. Grenoble office PHONE: (33)4 76 42 07 58

THE NETHERLANDS HORIBA UK Ltd. Nijmegen office PHONE: (31)24 301 0235

GERMANY HORIBA Europe GmbH PHONE: (49)351/889 68 07

SN-GE

Printed in Japan 1706SK13